
PROJECTED CAPACITIVE MODEL




DATE: 01/06/2016


REV: A


DIMENSIONAL DRAWING: ET1093L

PROJECTED CAPACITIVE MODEL

WITH FLUSH MOUNTING BRACKETS (4 SETS INCLUDED) REPLACEMENT BRACKET KIT P/N E511656 AVAILABLE SEPARATELY










INSTALLATION NOTES:

- 1. ATTACH BRACKET "A" TO TOUCHMONITOR (ALL FOUR SIDES) WITH LOW PROFILE SCREWS (INCLUDED)
 2. ATTACH BRACKET "C' TO CUSTOMER PANEL PER CUT-OUT DRAWING (ALL FOUR SIDES)
- 3. ATTACH BRACKET "B" TO BRACKET "C" (ALL FOUR SIDES) WITH M4 HEX HEAD SCREWS (INCLUDED)
 4. ADJUST DEPTH OF BRACKET "B" SO TOUCHSCREEN IS FLUSH WITH CUSTOMER PANEL
- 5. PLACE TOUCHMONITOR INTO CUSTOMER PANEL OPENING FROM FRONT SIDE
- 6. SECURE TOUCHMONITOR TO BRACKET "B" FROM BEHIND WITH M4 HEX HEAD SCREWS (INCLUDED)







SHEET 2 OF 2

MS601687 DATE: 01/06/2016